



# Radio - Device 1



**\*\* Note:**  
Instead of 1 pcs extension cable and 1 pcs split cable, you can use 2 pcs extension cables.



<b>Date of change:</b> 31. januar 2025	<b>Latest change:</b> -	<b>Changed by:</b> -	<b>Document name (pdf):</b> DRAW_90066	<b>Rev.no:</b> 002
<b>Date of creation:</b> 3. August 2020	<b>Subject:</b> Wir dgm SG sensor FA-FA-RA			
<b>Created by:</b> Magnus From	<b>Part no:</b> -			
<b>Date of approval:</b> 20-01-2022	<b>Scale:</b> -			
<b>Approved by:</b> Erik Kjærgaard	<b>Dimension:</b> -			
<b>Sense-Tech</b> Weighing Systems ApS Bygade 43 A - DK 7173 Vonge Tel. +45 76703001 - Fax +45 76703002 mail@sense-tech.com - www.sense-tech.com				
<b>Tolerance:</b> -				<b>Page x of x:</b> 1 af 1